

digital inspection camera

micro CA-350™

RIDGID

Application:

for detailed visual inspections in hard-to-reach spots.

Execution:

- 3.5 inch colour LCD display with 320 x 240 pixel resolution
- aluminium camera head with ultra-bright LED illumination
- flexible camera cable (watertight camera head and cable)
- images JPG: 640x480 pixels, video MP4: 640x480 pixels
- 12 V li-ion battery for longer running and shorter charge times
- incl. memory card 8 GB – expandable to 32 GB

Advantage:

- camera cable extendable up to 9 m using extensions
- digital 4x 90° screen rotation for upright image display



Art. no.	41500 103
Brand	RIDGID
Manufacturer Part Number	55903
Image rotation	360° (4 x 90°)
Display resolution	320 x 240 pix
Model	micro CA-350
Data transmission type	USB
Field of vision	72 Degree
Screen size	3.5 in
External memory on SD card	Up to 32 GB
Camera head diameter	17 mm
Number of LEDs	4 PCS
Cable length	0.9 m
Camera cable, extending	Yes
Speech recording	Yes
Image, video and audio recording	Image: 640 x 480 (jpg)/video: 640 x 480 (MP4)
Video output	PAL, NTSC
Number of rechargeable batteries/batteries	1 PCS
Battery designation	12 V lithium ion battery
Gross Weight	4.066 kg
Product Group	412

EAN

0095691559036