

Cabinet workbench, series V 4050

Universal coating 4050 mm, 12 drawers with full extension, 3 doors



Application:

For 3 workstations

Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 4 drawers with 100% full extension on the left, 2 x front height 90 mm, 2 x front height 180 mm, 1 door, height 540 mm on the right per workstation



Art. no.	50221 781
Brand	ANKE
Number of drawers	12 PCS
Working height	900 mm
Number of doors	3 PCS
Worktop width	4050 mm
Worktop height	50 mm
Pullout type	Full extension
Worktop depth	700 mm
Colour of front	Anthracite grey RAL 7016
Cabinet colour	Light grey RAL 7035
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Levelling	Yes
Lock type	DOM® locking system
Drawer front height	6 x 90 mm, 6 x 180 mm
Surface	Powder-coated
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	1500 kg
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of worktop	Universal covering
Central locking	Yes
Gross Weight	368.739 kg
Product Group	502

EAN

4014641162733