

Workbench trolleys

Working height 840 mm, with 4 drawers and 1 open compartment

Application:

The mobile workstation with versatile options for use.

Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick
- Suitable insert material for drawers, see from no. 50485 060-265 and from no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Advantage:

- When you buy this product, you plant a tree and also receive a tree certificate!
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50285 215
Brand	HK
Manufacturer Part Number	50285215
Number of fixed rollers	2 PCS
Working height	840 mm
Number of steering rollers	2 PCS
Worktop width	1155 mm
Number of drawers	4 PCS
Worktop height	40 mm
Worktop depth	700 mm
Pullout type	Partial extension
On castors	Yes
Moving device, can be lowered	No
Colour of front	Optional
Cabinet colour	Optional
With single pull-out safety brake	Yes
Surface	Powder-coated
With wheel lock	Yes
Load-carrying capacity	820 kg
Wheel diameter	200 mm
Type	mobile
Lock type	DOM® locking system
Material of worktop	Solid beech
Drawer front height	1 x 60 mm, 1 x 90 mm, 1 x 150 mm, 1 x 180 mm
Material	Sheet steel
Drawer width (inner dimension)	450 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	100 kg
Material of wheel	Solid rubber
Central locking	Yes
Gross Weight	109.000 kg
Product Group	501

EAN

4039247470631