conditions, remarks

nominal voltage: 12,0V

off load voltage 12,2... 12,8V new battery 12,2... 12,5V after 12 months

, ,

nominal capacity: 54mAh continuous discharge

under 20Kohm load 7,2V end discharge voltage ambient temperature 20...25°C

duration time:

under 20Kohm load

initial > 100hrs after 12 months > 90hrs 7,2V end discharge voltage


at 20°C

temperature range: -20... 60°C operating temperature 10... 30°C storage (recommended)

mechanical specifications:

weight approx. 7,5g

dimensions:







mechanical specifications(blister card):

dimension: 50mm x 70mm total weight: approx. 9g

18



specifications for model/type:	A23 Alkaline battery
Ansmann drawing number / part number:	5015182
	V1
author / date:	Gramlich / 13.08.2007