


# Power supplies – 19" AC/DC linear regulators

## LINEAR REGULATORS, DUAL



11300001



DLJM0084

### Connector pin-out

Pin	Connection
4	Sense line + V <sub>1</sub>
6	Output + V <sub>1</sub>
8	Output 0 V <sub>1</sub>
10	Sense line 0 V <sub>1</sub>
12	Sense line + V <sub>2</sub>
14	Output + V <sub>2</sub>
16	Output 0 V <sub>2</sub>
18	Sense line 0 V <sub>2</sub>
20	–
22	–
24	–
26	–
28	L
30	N
32	PE ⊕

- Mains/line voltage 230 V<sub>AC</sub> (can be switched to 115 V<sub>AC</sub> with mains/line voltage conversion kit)
- 2 output voltages, galvanically separated
- High control accuracy, low residual ripple and very low interference
- Suited for medical applications (8 mm safety clearances)

**CE** EN 62368-1  
approved

### DELIVERY COMPRISES

Qty	Description
1	19" compatible power supply Height 3 U Width A: 6, 10, 14 HP Depth 171.93 mm (160 mm board depth) Connector H 15M Coding strip (fitted)

### ORDER INFORMATION

Voltage V	Current A	Power W	Width HP	Description	Part no.
V1: 5 V2: 5	I <sub>1</sub> : 1.4 I <sub>2</sub> : 1.4	14	10	PSM 205	<b>13105-021</b>
V1: 12 V2: 12	I <sub>1</sub> : 0.4 I <sub>2</sub> : 0.4	10	6	PSK 212	13105-017
V1: 12 V2: 12	I <sub>1</sub> : 1 I <sub>2</sub> : 1	24	10	PSM 212	13105-022
V1: 12 V2: 12	I <sub>1</sub> : 1.5 I <sub>2</sub> : 1.5	36	14	PSG 212	<b>13105-027</b>
V1: 15 V2: 15	I <sub>1</sub> : 0.4 I <sub>2</sub> : 0.4	12	6	PSK 215	<b>13105-018</b>
V1: 15 V2: 15	I <sub>1</sub> : 1 I <sub>2</sub> : 1	30	10	PSM 215	13105-023
V1: 15 V2: 15	I <sub>1</sub> : 1.5 I <sub>2</sub> : 1.5	45	14	PSG 215	<b>13105-028</b>
V1: 24 V2: 24	I <sub>1</sub> : 1.2 I <sub>2</sub> : 1.2	58	14	PSG 224	<b>13105-029</b>
Front panel for PSK 6 HP, 1 piece					<b>21005-476</b>
Front panel for PSM 10 HP, 1 piece					<b>21005-477</b>
Front panel for PSG 14 HP, 1 piece					<b>21005-478</b>
EMC gaskets (stainless steel) 3 U, 97 mm, stainless steel, two pieces necessary per front panel, PU 10 pieces					<b>21101-705</b>
Connector H 15 F Mating connector (female) for wiring inputs/outputs (6.3 mm FASTON), 1 piece					<b>69001-733</b>
Coding PU (1 keying/coding strip, 2 pieces keying/coding pins)					<b>60800-123</b>
Coding PU (Female strip)					<b>60800-122</b>
Mains voltage conversion kit 230 V to 115 V, 1 piece					<b>43105-999</b>

### Note

- **Please order front panel separately** (Al, front anodised, rear iridescent green chromated, with vertical grooves for EMC gaskets, incl. assembly kit)
- PSK without case
- Output data at T<sub>A</sub> = 0 ... 50 °C
- Further accessories see page 9.15