

J.13 J - 3/8" metric 12-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

A [mm]:	13
d [mm]:	17,5
d1 [mm]:	18,3
L [mm]:	30
L1 [mm]:	10,4
12-Point [mm]:	12
[g]:	36

