

LK5

111-60519



T18S – T150XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties ensures a simple and quick installation. Whilst easily installed by hand manual, and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For routing, bundling and securing of cables, pipes and hoses.

Base Data

Colour

Natural (NA)

Label E-Number Finland

13 704 45

Label E-Number Norway

13 450 14

Label E-Number Sweden

15 162 16

Package Content

50

Quantity (Sold Unit / EDP)

50

Recommended Application Tool

MK9, MK9HT

Logisitic and Packaging

Carton Quantity

800

EAN code

4031026106960

Quantity of Europallet

12800

Weight (kg) (Metric)

18 kg

Material and Specifications

Flammability

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

Product Dimensions

Bundle Diameter max (Metric)

150

Bundle Diameter min (Metric)

12

Length L (Metric)

535

Minimum Tensile Strength (N)

1115

Width W (Metric)

13.2

© HellermannTyton 2006