

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2111760080](#)  
**Status:** **Active**  
**Overview:** [SlimStack Board-to-Board Connectors](#)  
**Description:** SlimStack Board-to-Board Plug, 0.35mm Pitch, Battery Series, 0.70mm Mated Height, 2.00mm Mated Width, 8 Circuits, 15.0A

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2111769200-SPK-200 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Guide (PDF)</a>
<a href="#">Product Specification 2111750000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2111750000-AS-000 (PDF)</a>	<a href="#">Reference Guide (PDF)</a>

**General**

Product Family	PCB Headers
Series	<a href="#">211176</a>
Application	Board-to-Board
Comments	* 15A of current per circuit is applicable if the circuit is constructed by two power circuits and one power nail via a PWB/FPC circuit.
Overview	<a href="#">SlimStack Board-to-Board Connectors</a>
Product Name	SlimStack
Series Name	Battery
UPC	193264110049

**Physical**

(p)ower-(s)ignal Configuration	4p - 4s
Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	0.70mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	7.163/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.3A, 5.0A*
-------------------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[211176 Series](#)

**Mates With**

[SlimStack Battery \(15.0A\) Receptacle  
2111750080](#)

Voltage - Maximum

50V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification

2111750000-AS-000

Packaging Specification

2111769200-SPK-200

Product Specification

2111750000-PS-000

Sales Drawing

2111760000-SD-000, 2111761000-SD-000

This document was generated on 12/04/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**