

Han Snap Plastic Housing Size 16B



Part number	09 33 016 0401
Specification	Han Snap Plastic Housing Size 16B
HARTING eCatalogue	https://b2b.harting.com/09330160401

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Snap [®]
Type of hood/housing	Shell housing

Version

Size	16 B
Version	Top/side entry
Locking type	Snap-in latches
Details	Size 16 A by using the corresponding adapter!
Pack contents	2 half shells with blind plugs

Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Retention force	≥300 N locked condition

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Material properties

China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal)
	IEC 60068-2-27 Shock

Commercial data

Packaging size	1
Net weight	48 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140051287
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors