

Specifications


Rated voltage	3VDC
Operating voltage	2-5VDC
Rated current*	≤30mA
Sound output at 10cm*	≥75dB
Resonant frequency	2700±300Hz
Operating temperature	-30~+70°C
Storage temperature	-40~+85°C
Weight	1.0g

*Value applying at rated voltage (VDC)

Features

- ROHS compliant
- Housing material: PBT
- Not Wave Solderable or Washable

All data at 25°C unless otherwise specified



Dimensions Unit: mm Tolerance: ±0.5mm



ALAN BUTCHER COMPONENTS LTD

Alan Butcher Components Ltd

Unit 1 Beechwood Clump Farm Industrial Estate Tin Pot Lane Blandford Dorset DT11 7TD

Telephone 01258 456360 Facsimile 01258 459194 Email sales@abcomponents.co.uk

www.abcomponents.co.uk



BS EN ISO 9001 Certification No 5239