

PRODUCT DATA SHEET

P/N 8750 0401 0

Crimping dies for use with following crimping tools and machines

 <p>Art. Nr. 8750 0000 6</p>  <p>Art. Nr. 8753 0000 6</p>		 
<p>P/N 8750 0000 6 (MicroCrimp) P/N 8753 0000 6 (DigiCrimp)</p>	<p>P/N 6700 0100 1 (incl. EU charger) P/N 670 0200 1 (incl. GB charger) P/N 6753 0000 6 (crimp unit)</p>	<p>P/N 636 025-3 (CM25-3 machine) P/N 636 0753 3 01 (crimp unit)</p>

Product Description Locator / Positioner with 12 positions for Harting, Ilme, HTS contacts and similar contacts

Product Image



Applications See table with settings below.
Contact P/N

Tool setting values

Mindestauszugswerte/ min. tensile strength		Hersteller / manufacturer													
		Kontakt / contact													
		Steck-Ø / plug-Ø													
		Locator / positioner (y)													
		Stift / pin													
		Buchse / socket													
		Einstellmaß / setting values* (X)													
Letzterschnitt/ wire size [mm ²]	Abzugswerte/ pull out forces [N] ¹	Walther	Walther	HTS	HTS	Contact	Contact	Contact	Weidmüller	Weidmüller	Weidmüller	Weidmüller	Weidmüller	Weidmüller	
0,14	18	1,6	3,6	1,6	2,5	1,6	2,5	3,6	HD	HE	CM5	CM3	CM3	HX	
0,25	32	1	5	1	2	1	2	5	1	2	6	5	3	3	
0,32	40	1,23	—	1,15	—	—	—	—	—	—	—	—	—	—	
0,50	60	1,26	—	1,20	—	—	—	—	1,30	—	—	—	—	—	
0,75	85	1,30	—	1,25	—	—	—	—	1,35	—	—	—	—	—	
1,00	108	1,30	—	1,30	1,30	1,30	1,30	—	1,40	1,40	—	—	—	—	
1,50	150	1,30	—	1,35	1,35	1,35	1,35	—	1,45	1,45	1,20	—	—	—	
2,10	200	1,40	—	1,40	1,40	1,40	1,40	—	1,50	1,50	1,25	—	—	—	
2,50	230	1,55	1,40	1,45	1,45	1,50	1,50	1,50	1,60	1,60	1,35	1,50	1,50	1,50	
3,30	275	1,80	1,60	1,60	1,70	1,65	1,65	1,65	1,75	1,75	1,50	1,65	1,65	1,65	
4,00	310	—	1,70	—	2,00	—	—	1,90	1,90	1,90	1,75	1,90	1,90	1,90	
6,00	350	—	1,90	—	—	—	—	2,20	—	—	—	2,10	2,30	—	
10,00	380	—	—	—	—	—	—	—	—	—	—	—	—	—	
0,14	18	1,20	—	1,15	—	—	—	—	—	—	—	—	—	—	
0,25	32	1,26	—	1,20	—	—	—	—	—	—	—	—	—	—	
0,32	40	1,30	—	1,25	—	—	—	—	—	—	—	—	—	—	
0,50	60	1,30	—	1,30	1,30	1,30	1,25	—	1,40	1,40	—	—	—	—	
0,75	85	1,30	—	1,35	1,35	1,35	1,30	—	1,45	1,45	1,20	—	—	—	
1,00	108	1,40	—	1,40	1,40	1,40	1,35	—	1,50	1,50	1,25	—	—	—	
1,50	150	1,55	1,40	1,45	—	1,50	1,45	1,45	1,60	1,60	1,35	1,50	1,50	1,50	
2,10	200	1,80	1,60	1,60	1,70	1,65	1,65	1,65	1,75	1,75	1,50	1,65	1,65	1,65	
2,50	230	—	1,70	—	2,00	—	—	1,90	1,90	1,90	1,75	1,90	1,90	1,90	
3,30	275	—	1,90	—	—	—	—	2,20	—	—	—	2,10	2,30	—	
4,00	310	—	—	—	—	—	—	—	—	—	—	—	—	—	
6,00	350	—	2,00	—	—	—	—	—	—	—	—	—	—	—	
10,00	380	—	—	—	—	—	—	—	—	—	—	—	—	—	

