
PERFORMANCE **III** LIGHTING



ART.: 8432154136410 **EB432 LED SPOT REFLECTOR**





Art.: 8432154136410, EB432 LED, 14W, 4000K, Driver dali, Direct / spot (2 x 0°-10°), White, Recessed LED luminaire for indoors, consisting of: Die-cast aluminum spotlight body and ring, powder-coated, Reflector can be swivelled horizontally inwards and outwards thanks to the unique swivel mechanism, Adjustable about 60° (from -15° up to 45°, rotatable about 355°, High-brilliance spherical faceted reflector for maximum lamp performance and neutral colour rendering, Reflector in Spot design, Colour rendering index Ra > 90, Colour tolerance according to MacAdam ≤ 3 SDCM Toolless mounting, Complete with electric converter, Anchor springs, Complete with clear safety glass pane

Connected load 14 W **Luminous flux** 1380 lm **Efficiency** 98 lm/W Colour temperature 4000K Colour rendering (CRI) 80 **IP class** 20 **Nominal voltage**

220 - 240 V Colour **RAL 9010**

