

KBU 35 Q magnetic core drill

1100 W with QuickIN holder



Application:

For drilling large diameters on magnetic workpieces.

Execution:

- electronic speed adjustment
- Clockwise/anti-clockwise rotation
- integrated coolant tank
- Manual feed wheel can be positioned on either side
- Tilt sensor
- Speed memory "Memory Function"

Advantage:

- small, lightweight and powerful

Delivery:

incl. coolant tank, lashing strap, swarf hook, centring pin, in plastic case



Art. no.	70145 011
Brand	FEIN
Manufacturer Part Number	72705361000
Model	KBU 35 Q
Type	universal
Battery included	No
Number of rechargeable batteries/batteries	0
Tool holding device	QuickIN
Max. drilling diameter of core drill bit in steel	35 mm
Max. drilling diameter in steel	16 mm
Max. drilling depth	50 mm
Max. idle speed	130 rpm
Min./max. rotation speed at nominal load in 1st gear	130-520 rpm
Max. thread-cutting performance	M36
Max. countersunk diameter	31 mm
Power input	1100 W
Power output	550 W
Baseplate width	175 mm
Baseplate length	80 mm
Max. working stroke	260 mm
Adherence strength	10000 N
Weight	10.6 kg
Gross Weight	17.130 kg
Product Group	704

EAN

4014586886039