



Identification


Fibre optic cable,
PushPull V4 – SC duplex,
multi mode, 62.5 / 125 µm
overmoulded

Length:	a =	Part number
	1 m	33 61 431 0010 006
	2 m	33 61 431 0020 006
	3 m	33 61 431 0030 006
	4 m	33 61 431 0040 006
	5 m	33 61 431 0050 006
	6 m	33 61 431 0060 006
	7 m	33 61 431 0070 006
	8 m	33 61 431 0080 006
	9 m	33 61 431 0090 006
	10 m	33 61 431 0100 006
	11 m	33 61 431 0110 006
	12 m	33 61 431 0120 006
	13 m	33 61 431 0130 006
	14 m	33 61 431 0140 006
	15 m	33 61 431 0150 006
	20 m	33 61 431 0200 006
	25 m	33 61 431 0250 006
	30 m	33 61 431 0300 006
	35 m	33 61 431 0350 006
	40 m	33 61 431 0400 006
	45 m	33 61 431 0450 006
	50 m	33 61 431 0500 006
	60 m	33 61 431 0600 006
	70 m	33 61 431 0700 006
	80 m	33 61 431 0800 006
	90 m	33 61 431 0900 006
	100 m	33 61 431 1000 006


Part number

Drawing



Dimensions in mm



a = length



Loading-Plan



Fibre optic breakout cable,
multi mode, 62.5 / 125 µm

Length: 10 m	33 58 751 0100 001
Length: 20 m	33 58 751 0200 001
Length: 100 m	33 58 751 1000 001



PUR jacket
2-fibre multi mode 62.5 µm
Outer diameter: 7 mm
Min. bending radius:
Installation: 10.5 cm
Operating: 7.0 cm