


PX0599 Datasheet

Product Name // Straight Female C19 IEC Connector
PX0599 Screw Terminals EN60 320-1 Standard Sheet C19
Class I

[View Product Page](#)


// Product Description:

- ⊞ Straight Female C19 IEC Connector
- ⊞ EN60 320-1 Standard Sheet C19 Class I and Standard Sheet C20 Class I
- ⊞ Cold Condition
- ⊞ Cable mount
- ⊞ Screw Terminal (rewireable)
- ⊞ Mate with PX0596, PX0598

// General Information:

Product Configurator:	No
Product Display Title:	Straight Female C19 IEC Connector
Product Family:	IEC Connectors
Product Series:	IEC60320 Main Inlets and Outlets
Pdfbuilder Enabled:	Yes
Approvals:	CSA, ENEC, UL, VDE
Function:	Straight Female Connector
iec Connector Mates With:	PX0596,PX0598
iec En60620 Type:	EN60 320-1 Standard Sheet C19 Class I
Max Operating Temperature:	+70°C
Min Operating Temperature:	-40°C
Number Of Contacts:	3 Contacts
Product Technical Image:	/p/x/px0599_diagram.jpg
Package Id:	564

// Electrical Specifications:

Current Max:	16A, 20A
Voltage Max:	250V

// Material Information:

Body Material:	Nylon 66
Flamability Rating:	UL94V-0

// Product PDF Links

[IEC Connectors product data](#)
[PX0599 IEC connector wiring...](#)

// Product 3D CAD Model Links

[PX05993D CAD Model](#)

// Product Certificate Links

[VDE Certificate](#)
[UL E70394 Certificate](#)
[CE Certificate](#)