

[Products](#) [Multimeter](#) [Digital handheld multimeter](#) [PeakTech® 1070](#)

## PeakTech® 1070 PROD-ID: P 1070

[BACK](#)

### Digital Multimeter ~ 2.000 Counts ~ 300V AC/DC ~ 10A DC ~ TÜV/GS

TÜV/GS approved pocket size digital multimeter in modern design. Suitable for technicians and hobbyists.

- 3 ½ digit, 12 mm LCD-display, max. 1999
- Current measurements up to 10 A DC
- Diode- and continuity test
- Temperature measurements
- Safety: TÜV/GS; EN-61010-1; CAT III 300 V
- Accessories: test leads, type K-thermocouple probe, battery and operation manual



#### MANUAL

[PeakTech\\_1070\\_05-2018.pdf \(331.4 kB\)](#)

#### PICTURES

[1070\\_Front.jpg \(371.5 kB\)](#)

[1070\\_L\\_freigestellt.jpg \(1,018.4 kB\)](#)

[1070\\_R\\_freigestellt.jpg \(1,258.6 kB\)](#)

DCV	200/2000 mV/20/200/300 V; $\pm 0,8\%$ + 2 dgt.
ACV	200/300 V; $\pm 1,2\%$ + 10 dgt.
DCA	200/2000 $\mu$ A/20/200 mA/10 A; $\pm 1,0\%$ + 2 dgt.
Ohm	200/2000 $\Omega$ /20/200/2000 k $\Omega$ ; $\pm 0,8\%$ + 2 dgt.
Temperature	0 ... 1000 °C; $\pm 2,0\%$ + 3 dgt.
Operation Voltage	9 V-battery
Dimensions (WxHxD)	70 x 140 x 30 mm
Weight	120 g
EAN-13	4250569400100

