

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200060015](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 0.34mm² Black PVC Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120006](#)
 Connector End A Micro-Change (M12)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Protocol N/A
 Region Europe
 Type Single Ended
 UPC 800756927350

Physical

Cable Diameter 5.40mm (.213")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Female-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Net Weight 213.980/g
 Orientation Straight to Pigtail
 Poles 4
 Temperature Range - Operating -30° TO +80°C
 Wire Size AWG 22
 Wire/Cable Type UL 2464

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V

Material Info

Engineering Number 804000E03M050

Reference - Drawing Numbers

Sales Drawing 1200651978-000



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000380967_00_000.pdf

Search Parts in this Series

[120006 Series](#)

This document was generated on 01/10/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION