



## Product Information

Product Category	HOBS
Unit Barcode	5016368078174
Outer Carton Barcode	
Commodity Code	8516605000
Country of Origin	CHINA
Primary Colour	BLACK
Finish	GLASS
Primary Material	CERAMIC
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

## General Product Specification

Voltage	230
Frequency	50
Wattage	6800
Rated Current	30
Fuse Rating	32
Plug Type	
Cable Diameter	1.5
Cable Length	1
Class	CLASS I
Conformity Markings	CE+UKCA

## Packaging &amp; Shipping Information

Product Dimensions H x W x D (mm)	58	590	520
Packaged Dimensions H x W x D (mm)	115	650	580
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			7.95
Unit Packaged Weight (Kg)			9.1
Carton Weight (Kg)			
EPS (Kg)	1.069	PPT Exempt Plastic (Kg)	0.027
Other Plastic (Kg)	0.158	Card / Paper (Kg)	
Aluminium (Kg)		Steel (Kg)	

## Category Specific Technical Information

Auto-Shut Off Timer	YES	Number of 145mm Hotplates/ Vitroceramic Zones	
Auto-Shut Off Timer Length	120	Number of 180mm Hotplates/ Vitroceramic Zones	1
Child Lock	YES	Rear Left Hotplate/ Vitroceramic Zone Size	160
Control Panel Position	FRONT	Rear Left Hotplate/ Vitroceramic Zone Power	1.4
Control Type	TOUCH	Rear Right Hotplate/ Vitroceramic Zone Size	180
Fuel Type	ELECTRIC	Rear Right Hotplate/ Vitroceramic Zone Power	1.8
Hob Surface Material	GLASS	Front Left Hotplate/ Vitroceramic Zone Size	210
Hob Type	INDUCTION	Front Left Hotplate/ Vitroceramic Zone Power	2.2
Ignition Type		Front Right Hotplate/ Vitroceramic Zone Size	160
Number of Burners / Zones	4	Front Right Hotplate/ Vitroceramic Zone Power	1.4
Number of Heat Settings	9	Middle Hotplate/ Vitroceramic Zone Size	
Pan Support	NO	Middle Hotplate/ Vitroceramic Zone Power	
Pan Support Type		Total Cooktop Hotplate/ Vitroceramic Zone Power	6.8
Pre-Fitted 3 Core Cable	NO		
Total Number of Hotplates/ Burners/ Vitroceramic	4		