

# 80105 Bendable probe Ø1.5mm, L=130mm



## General

Toepassing	Sensor for general use
Construction	Round tip 1.5 mm
Handgreep	ABS plastic
Use	Primarily for gas, liquid and flame temperature
Plug	Flexible, 300 mm

## Sensor

Thermokoppel	Type K
Nauwkeurigheid	Volgens IEC 584-1
Responsietijd	6 seconds
Max. tip temperatuur	900°C / 1652°F

## Sensor

Material	Stainless steel
Probe lengte	130 mm
Tip diameter	1,5 mm

## Cable

Aansluitkabel	Coiled cable, polyurethane insulated
Kabellengte	1000 mm
Type	K
Color	Black
Connector	Miniature thermocouple connector, flat pins

## Options

Cable color	IEC / ANSI
Connector kleur	IEC / ANSI

