

MILAN S.r.l. a socio unico


Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it



Technical Datasheet

tasker® C211 – 3x0,25 mm² - LiYCY Cable



CATEGORY NOTE

Shielded Cable for Electronics and Data (See Data Network Catalogue)
 The picture don't represent the real number of conductors.

- A:** Grey Soft **PVC** Sheath. - Outer cable Ø: 4,70 (±0,10) mm.
- B:** Braided Shielding in O.F.C. Tinned Copper, covering 85% + Drain Wire.
- C:** Cores Insulation with Soft **PVC**– DIN 47100 Standards.
 Color Code: White, Brown, Green. Diam. Ø 1,30 (±0,10) mm.
 Stranded with waste filler between conductors and wrapped with Mylar Tape.
- D:** Stranded O.F.C. Red Copper formation 14x0,15 mm.
 Nom. Cross section 3x0,25 mm².

MARKING CUSTOM

tasker® C211 LiYCY 3x0,25 – 23 AWG Low Voltage Computer Cable made in Italy
 This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	75 Ω/Km ± 5%
Capacity Core/Core	100 pF/mt
Capacity Core/Shield	190 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 08.07.2016
		Outdoor Direct Burial	Esterno Interrato			Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			