

Category 5e tool-less component level keystone socket



CAT 5e tool-less component level keystone (FKF*)

Our Category 5e jack offers a tool-less keystone solution for any Category 5e requirement, available as a panel mount version (FKFbkpm).

Features








- High performance data throughput, meets Category 5e data transfer rates at component level
- UTP socket to FCC68 standard
- Quick, easy and reliable tool-less termination with 'butterfly' style levers
- Standard format keystone fits a wide range of panels, adaptors and faceplates
- Category 6 version in various colours also available (SKF*)
http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pId=173
- Panel mount version supplied with adaptor KApma:
http://www.tuk.co.uk/tuk_live/product_details.php?category_id=15&pId=204

Specifications

- Weight: approx 11g
- Colour: black
- Materials: 50µ"/1.27µm gold plating on contact
- Housing: ABS UL94V-0

LIMITS	CLASS	DEGREE			
		A	B	C	D
10 以下		±0.02	±0.05	±0.10	±0.15
10~50 以下		±0.05	±0.10	±0.15	±0.20
50~120 以下		±0.10	±0.15	±0.20	±0.25
120~300 以下		±0.15	±0.20	±0.25	±0.30
300~500 以下		±0.20	±0.25	±0.30	±0.35
500~1000 以下		±0.25	±0.30	±0.35	±0.40
1000~1500 以下		±0.30	±0.35	±0.40	±0.45
ANGEL		±0.2°	±0.5°	±1.0°	±1.5°

ZONE	REV.	DESCRIPTION	DATE	APPROVED
A3,B4	A		08.04.09	



ELECTRICAL
 CURRENT RATING : 1.5A
 DIELECTRIC WITHSTANDING VOLTAGE : 1000VAC 60Hz
 INSULATION RESISTANCE : 500M Ω MIN.
 CONTACT RESISTANCE : 20m Ω MAX.
 MECHANICAL
 (1) Materials: UV stabilized PC+ABS, and polycarbonate
 (2) RJ45 Jack Contact: Phosphor bronze, 50u" Gold Plating
 (3) Cavity conforms to FCC rules and Regulations Part 68

DRAWN:		PART NO.		UNIT		MM	
		FKF*					
DESIGNED:		MATERIAL		SCALE		1 : 1	
CHECKED:		FINISH		SHEET		1 OF 1	
APPROVED:		TOOLING NO.		SIZE		A4 REV. A	
TITLE:		DWG NO.		REV.		A	
Keystone Jack		TUK Ltd					

