



UT210 SERIES Mini Clamp Meters

UT210A / UT210B / UT210C (new)



UL61010-1
EN61010-1
EN61010-2-032
EN61010-2-033
EN61326-1



■ UT210A



■ UT210B



■ UT210C

SPECIFICATIONS



Specifications	Range	Best Accuracy		
Model		UT210A	UT210B	UT210C
AC Current (A)	2A/20A/200A	±(1.0%+9)	±(1.0%+9)	
	20A/200A			±(1.8%+9)
AC Voltage(V)	2V/20V200V/600V			±(1.0%+3)
DC Voltage(V)	200mV/2V/20V200V/600V			±(0.7%+3)
Resistance(Ω)	200Ω/2kΩ/20kΩ/200kΩ/2MΩ/20MΩ			±(1.0%+2)
Capacitance (F)	20nF/200nF/2μF/20μF/200μF/2mF/20mF			±(4%+5)
Temperature(°C)	-40~1000°C			±(1%+3)
Temperature(°F)	-40~1832°F			±(1.5%+5)
Features				
Display Count		2000	2000	2000
Auto Range				✓
Jaw Capacity		17mm	17mm	17mm
True RMS			✓	✓
Diode	Around 3.0V			✓
NCV			✓	✓
Data Hold		✓	✓	✓
MAX/MIN			✓	✓
Relative Mode			✓	
LCD Backlight		✓	✓	✓
Auto Power Off	Around 15 Minutes	✓	✓	✓
Continuity Buzzer				✓
Low Battery Indication	≤2.5V	✓	✓	✓
Input Protection		✓	✓	✓
Input Impedance for DCV	≥10MΩ			✓

GENERAL CHARACTERISTICS

Power	AAA 1.5V x 2
LCD Size	39.3mm x 26.5 mm
Product Color	Red and Grey
Product Net Weight	UT210A/B - 160g UT210C - 170g
Product Size	UT210A/B - 155mm x 60mm x 33.5mm UT210C - 175mm x 60mm x 33.5mm
Standard Accessories	UT210A/B - Batteries UT210C - Batteries, Test Lead, Point Contact Temperature Probe
Standard Individual Packing	UT210A/B - Gift Box, English Manual UT210C - Gift Box, Carrying bag, English Manual
Standard Quantity Per Carton	40PCs
Standard Carton Measurement	UT210A/B - 345X245X300mm (0.025 CBM Per Standard Carton) UT210C - 385X345X305mm (0.041 CBM Per Standard Carton)
Standard Carton Gross Weight	UT210A/B - 9.5kg UT210C - 11kg