

POTENTIAL TERMINAL BLOCK GRAY

Potential terminal block
gray/gray/gray/gray

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

General data

Protection	IP20
Dimensions H × W × D	70×56×32.5 mm
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)
Temperature range	0...+55 °C (storage temperature -40...+85 °C)

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1