


LED-INDICATOR GREEN


LED 3mm - 24V DC -20 mA- IP40

(green)
24 V DC

[Link to Product](#)

Illustration





Product may differ from Image

Technical Data

Operating voltage	24 V DC \pm 15 %
Current consumption	approx. 15 mA
Protection acc. to (IEC 60529/EN 60529)	IP40

General data

Connection	Faston 2.0 \times 0.5 mm
Housing	Brass, chrome plated
LED \varnothing	3 mm
Front panel hole diameter \varnothing	6 mm
Dimensions H \times W \times D	7 \times 7 \times 33 mm
Temperature range	-40...+70 °C

Commercial data

country of origin	DE
customs tariff number	85414010
minimum order quantity	10