

Product type designation

Bus terminal RS 485 (3m)

RS 485 BUS TERMINAL FOR PROFIBUS TRANSMISSION RATE
9.6 KBIT/S TO 1500 KBIT/S WITH CONNECTING CABLE 3.0 M



Electrical data

Transfer rate / with PROFIBUS	9.6 kbit/s ... 1.5 Mbit/s
-------------------------------	---------------------------

Interfaces

Number of electrical connections	2
<ul style="list-style-type: none"> • for PROFIBUS cables 	
Type of electrical connection	Screw terminals
<ul style="list-style-type: none"> • for PROFIBUS cables 	

Mechanical data

Material / of the enclosure	plastic
-----------------------------	---------

Design, dimensions and weight

Width	50 mm
Height	138 mm
Depth	53 mm
Net weight	360 g
Mounting type	Yes
<ul style="list-style-type: none"> • 35 mm DIN rail mounting 	

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/automation/net/catalog

- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015