

IWLAN RCOAX N-CONNECT/N-CONNECT FEMALE/ FEMALE
 PANEL FEEDTHROUGH 2.4GHZ AND 5 GHZ CABINET CABLE
 DUCT FOR WALL THICKNESS MAX. 4.5MM



Electrical data

Number of electrical connections	2
Type of electrical connection	N-Connect female/N-Connect female
Transmission frequency	0 ... 11 GHz
Impedance	50 Ω

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport 	-30 ... +100 °C -30 ... +100 °C -30 ... +100 °C
Protection class IP	IP 68

Design, dimensions and weight

Diameter	20.7 mm
Length	38 mm
Net weight	55 g

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL to website: Industrial communication 	http://www.siemens.com/snst http://www.siemens.com/simatic-net

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015