

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5023520400**
Status: **Active**
Overview: DuraClik Connector System
Description: DuraClik Wire-to-Board Header, Single Row, Right-Angle, 4 Circuits, Tin (Sn) Plating, Natural

Documents:

| | |
|---|--|
| 3D Model | Packaging Specification PK-502352-002-JP-001 (PDF) |
| Drawing (PDF) | Packaging Specification SPK-502352-001-001 (PDF) |
| Product Specification PS-502351-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|----------------|--|
| Product Family | PCB Headers |
| Series | <u>502352</u> |
| Application | Signal, Wire-to-Board |
| Comments | The Operating Temperature Range when used with DuraClik series 502351 is -40°C to +105°C. It is -40°C to 125°C when used with DuraClik ISL series 560123 or TPA series 505151. |
| Overview | <u>DuraClik Connector System</u> |
| Product Name | DuraClik |
| UPC | 800756731728 |

Physical

| | |
|--------------------------------|-----------------------|
| Breakaway | No |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Mated Height | 6.40mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin over Nickel |
| Material - Resin | Polyamide |
| Net Weight | 595.000/mg |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Surface Mount |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 125V |

Solder Process Data

| | |
|--|-----|
| Duration at Max. Process Temperature (seconds) | 004 |
|--|-----|



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

502352 Series

Mates With

DuraClik Crimp Housings 502351 , 560123 , 505151

Lead-free Process Capability
Max. Cycles at Max. Process Temperature
Process Temperature max. C

REFLOW
001
255

Material Info

Reference - Drawing Numbers

Packaging Specification
Product Specification
Sales Drawing

PK-502352-002-JP-001, SPK-502352-001-001
PS-502351-001-001
SD-502352-001-001, SD-502352-002-001

This document was generated on 10/18/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION