

Product information

98 33 25

Torque Wrench

With driving square, reversible

ISO 3315 IEC 60900 DIN EN 60900

- Transparent insulated scale range 5 - 25 Nm
- Reversible for tightening of lefthanded threads
- Lockable torque adjustment
- Adjustable in steps of 0.25 Nm
- Easy and secure locking of attached sockets due to screw lock
- Calibration certificate included
- Chrome Vanadium steel



⚡ 1000 V 

General

| | |
|-----------------|---------------------------------|
| Article No. | 98 33 25 |
| EAN | 4003773072676 |
| Weight | 1,230 g |
| Dimensions | 290 x 85 x 55 mm |
| Standard | ISO 3315 DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|----------------------|-----------|
| Square drive | 3/8 |
| Range of Application | 5 - 25 Nm |

technical change and errors excepted