




Description

The model 710 AC hour meters and minute meters are widely used in panel applications where number size and visibility are critical. Its tough, Lexan bezel and distinctive styling enhance appearance and durability. Available in 5 figure reset or 6 figure non-reset versions.


Features		Options	
 Large figures Tough, Lexan case Reset or non-reset Specifications		 Private label faceplates Bracket mount Mounting bracet (721-0003) Splash proof kit (721-0017) Heavy duty splash proof kit (721-0018) Gasket (721-0004) 	
Figures: Reset: Voltages: Power: Mounting:	5 figures, 9999.9 (reset) or 6 figure, 99999.9 (non-reset), 0.19" [5mm] high Reset (on front or side) or non-reset 24, 115 or 230VAC, (+/-10%), 50 or 60 Hz. 3 watts (nominal) Panel (3-hole)	Terminations Temp. Range Approvals: Weight:	
Models	Description	Models	Description
710-0001 710-0002 710-0003 710-0006 710-0008 710-0009 710-0013	115VAC/60Hz, non-reset, 99,999.9 hrs, 8" [203mm] wire leads 115VAC/60Hz, non-reset, 99,999.9 hrs, terminal block 230VAC/60Hz, non-reset, 99,999.9 hrs, 8" [203mm] wire leads 24VAC/60Hz, non-reset, 99,999.9 hrs, 8" [203mm] wire leads 115VAC/60Hz, non-reset, 99,999.9 hrs, 8" [203mm] wire leads 115VAC/50Hz, non-reset, 99,999.9 hrs, 8" [203mm] wire leads 115VAC/60Hz, front reset, 9,999.9 hrs, 8" [203mm] wire leads 115VAC/60Hz, front reset, 9,999.9 hrs, 8" [203mm] wire leads 115VAC/60Hz, front reset, 9,999.9 hrs, 8" [203mm] wire leads	710-0014 710-0018 710-0024 710-0026 710-0032 710-0051	230VAC/60Hz, non-reset, 99,999.9 hrs, terminal block 115VAC/60Hz, non-reset, 99,999.9 min, 8" [203mm] wire leads 24VAC/60Hz, non-reset, 99,999.9 hrs, terminal block 115VAC/50Hz, non-reset, 99,999.9 hrs, terminal block 115VAC/60Hz, front reset, 9,999.9 hrs, terminal block 115VAC/60Hz, non-reset, 99,999 hrs, terminal block
terns in bold are normally in factory stock.			

Dimensions



Mounting holes: For #4 screws on 2.44" [62.0] B.C. and #6 screws on 2.53" [64.3] B.C. Panel cutout: 2.21" [56.1] Dia.

Applications



www.redingtoncounters.com