



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKT XCMD XCKP XCKD

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated body	ZCP29 ZCD39 ZCP26 ZCMD69C12 ZCD21M12 ZCMD29L2 ZCMD39L5 ZCD27 ZCMD29C12 ZCT25G11 ZCT28N12 ZCMD21M12 ZCP21M12 ZCD28 ZCMD61C12 ZCT27N12 ZCMD21C12 ZCMD81L5 ZCT27G11 ZCT26P16 ZCMD21L2 ZCT25N12 ZCP25 ZCP29M12 ZCT27P16 ZCT21P16 ZCD35 ZCMD41L2 ZCD29M12 ZCMD25L5 ZCMD21L08U78 ZCT21G11 ZCT28G11 ZCP31 ZCMD37L5 ZCD29 ZCT26N12 ZCMD39L2 ZCP21 ZCT25P16 ZCP37 ZCMD61M12 ZCD37 ZCP39 ZCMD25L2 ZCMD37L2 ZCP35 ZCT26G11 ZCD26 ZCMD41L1 ZCD25 ZCMD29L1 ZCMD39L1 ZCP27 ZCMD41L5 ZCMD81L2 ZCD31 ZCMD37L1 ZCMD21L1 ZCMD29L5 ZCMD25L1 ZCMD21L5 ZCT28P16 ZCD21 ZCP28 ZCMD81L1 ZCT21N12 ZCMD21L08R12
Movement of operating head	Linear
Type of operator	Roller lever plunger spring return metal retractable)
Type of approach	Lateral approach, 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901577737
Nbr. of units in pkg.	1
Package weight(Lbs)	0.07 lb(US) (0.03 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Package 1 Height	0.200 dm
Package 1 width	0.500 dm
Package 1 Length	0.350 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------