

Ball valve

for stainless steel jointed hose systems

ORION[®]

Application:


For blocking and regulating the coolant flow.

Version:

- suitable up to at least 40 bar operating pressure
- connecting thread to fit every machine
- SW 11 and 16 width across flats on 6-mm system
- Clamping width 14 and 20 across flats on 8.8-mm system

Advantage:

- extremely long service life
- resistant to temperature and chemical substances
- fully rigid and individually adjustable thanks to screw coupling



Art. no.	18300 446
Outer thread dimension	G 3/8 inch
Inner thread dimension	G 1/4 inch
System design	6 mm, 8.8 mm

EAN-Code

4053625199167