

Electronic pocket vernier callipers

TWIN-CAL IP40



Application:

For measuring external, internal, step and depth dimensions.

Execution:

- With locking screw
- ON
- mm/inch changeover
- Auto off
- Zero setting at any position
- ABS function

Advantage:

- Long operating time of over 12,000 hours

Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



Art. no.	31172 115
Brand	TESA
Manufacturer Part Number	00530097
Min./max. length measuring range	0-150 mm
Data transmission type	TLC
Depth gauge rod	Flat
IP protection class	IP 40
With drive wheel	No
Length of jaw	40 mm
Digit height	11 mm
Length of cross tips	16 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
With mm / inch switching	Yes
Battery designation	3V CR2032 Lithium
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.003 kg
Battery voltage	3 V
Type of rechargeable battery/battery	Lithium
Calibration Group	A
ISO	13385-1
Type	TWIN-CAL IP40
Gross Weight	0.329 kg
Product Group	362

EAN

7630041106176