

Electronic outside micrometer

With hardened tips

Mitutoyo

Application:

For measuring grooves, distances etc.

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65
- Digimatic

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Including box, set standard (from 25 mm) wrench, battery



Art. no.	32017 599
Brand	MITUTOYO
Manufacturer Part Number	342-35 1-30
Display	Digital
Min./max. length measuring range in inches	0-1 in
Digit increment	0.00005 in
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Automatic switch-off
Min./max. measurement force	3-8 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	32.5 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	0.540 kg
Product Group	3MA

EAN

4946368689043