

LED machine and workstation lamp 230 V

Infinitely adjustable focus for spot or wide beam, IP 20

ATORN[®]

Version

- Voltage 230 V, 50 Hz
- Lamp head and base made from impact-resistant, non-flammable plastic
- Anodised aluminium star-shaped heat dissipator and lens holder
- Switch integrated in the lamp head
- colour temperature 4000 K
- Enormous light output and long LED service life
- 1.6-m connection cable

Advantage

- Infinitely adjustable focus for spot or wide beam

Delivery

With extra-strong magnetic clamp and screw clamp with star-shaped grip



Art. No.	56870 010
Power rating	3 W
Arm length	590 mm
IP protection class	IP 20

EAN-Code

4050293342963

