



Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

**Hybrid fibre optic cable, multi mode, double ended**  
2 x G50/125 + 3 x 2.5 mm<sup>2</sup>

Length: a = 1 m AC version  
DC version

a = 5 m AC version  
DC version

a = 10 m AC version  
DC version

a = 20 m AC version  
DC version

a = 40 m AC version  
DC version

a = 50 m AC version  
DC version

a = 100 m AC version  
DC version

33 57 211 0015 001  
33 57 211 0015 002

33 57 211 0055 001  
33 57 211 0055 002


33 57 211 0105 001  
33 57 211 0105 002

33 57 211 0205 001  
33 57 211 0205 002


33 57 211 0405 001  
33 57 211 0405 002

33 57 211 0505 001  
33 57 211 0505 002

33 57 211 1005 001  
33 57 211 1005 002



a = length



Protection level: IP65/IP67

**Hybrid fibre optic cable, multi mode, single ended**  
2 x G50/125 + 3 x 2.5 mm<sup>2</sup>

Length: a = 1 m AC version  
DC version

a = 5 m AC version  
DC version

a = 10 m AC version  
DC version

a = 20 m AC version  
DC version

a = 40 m AC version  
DC version

a = 50 m AC version  
DC version

a = 100 m AC version  
DC version

33 57 111 0015 001  
33 57 111 0015 002

33 57 111 0055 001  
33 57 111 0055 002


33 57 111 0105 001  
33 57 111 0105 002

33 57 111 0205 001  
33 57 111 0205 002

33 57 111 0405 001  
33 57 111 0405 002

33 57 111 0505 001  
33 57 111 0505 002

33 57 111 1005 001  
33 57 111 1005 002



a = length

**Hybrid fibre optic cable, multi mode, 50 µm**

Length: 10 m

Length: 20 m

Length: 500 m

33 57 851 0100 002

33 57 851 0200 002

33 57 851 5000 002

PVC jacket

2 x G50/125 + 3 x 2.5 mm<sup>2</sup>

Outer diameter: 12.6 mm

Min. bending radius:  
single: 5 x OD  
repeated: 10 x OD