



*Monocular microscope, 400x,  
achromatic objectives*

<b>Observation Method - Transmitted Light</b>	Brightfield	Yes
	Simple polarized light	As optional
<b>Main Body</b>	Type	Upright
	Construction material	Aluminum die-cast
	Transportation handle	Yes
<b>Head</b>	Type	Monocular
	Inclination	45°
	360° rotating	Yes
	Fixing screw for eyepieces	Yes
	Tube inner diameter (mm)	23
<b>Eyepieces</b>	Field number (mm)	18
	Magnification	10x
	Pointer	As optional
	Micrometric scale	As optional
<b>Nosepiece</b>	Positions	Quadruple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
<b>Objectives</b>	Optical system	160
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	35
	Standard magnifications	40x-400x
	Type	Achromatic
		4x/0.10, W.D. 10.6 mm
		10x/0.25, W.D. 7.0 mm
	40x/0.65, W.D. 0.5 mm	
<b>Stage</b>	Type	Fixed
	Dimensions (mm)	120x110
	Moving mechanism	As optional
	Material	Anti-scratch painting
	Specimen clips	Yes
	Slide number	1
<b>Condenser - Single Position</b>	Type	Fixed
	Numerical aperture (N.A.)	0.65
	Diaphragms	Iris
<b>Focusing System</b>	Type	Coaxial coarse & fine
	Coarse total travel (mm)	23
	Fine total travel (per single rotation) (mm)	1.2
	Fine graduations	100
	Fine resolution (µm)	12
	Upper stop to prevent contact	Yes

<b>Transmitted Illumination</b>	Type	LED
	Light source power (W)	1
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	1.5

<b>Power Supply for Transmitted Illumination</b>	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	5 Vdc 500 mA
	Rechargeable batteries	Yes
	Battery type	Ni-MH (3x, AAA size)
	Working time of batteries (hours)	4
	Charging time of batteries (hours)	8

<b>Accessories Included</b>	Dust cover	Yes
	User Manual	Digital version (downloadable)

<b>Additional Information</b>		Plane concave mirror (as optional)
-------------------------------	--	------------------------------------

<b>Product Dimensions</b>	Height (mm)	330
	Width (mm)	135
	Depth (mm)	235

<b>Product Weight</b>	(kg)	2.6
-----------------------	------	-----