

**H0,5/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For conductors from 0,25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

**General ordering data**

Type	H0,5/6
Order No.	<a href="#">028260000</a>
Version	Wire end ferrule, 0.5 mm <sup>2</sup>
GTIN (EAN)	4008190184025
Qty.	1,000 pc(s).

**Datenblatt**

**H0,5/6**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	6 mm	Net weight	0.029 g
--------	------	------------	---------

**Product data**

Conductor cross-section	0.5 mm <sup>2</sup>	Wire connection cross section AWG, max.	AWG 20
Contact surface diameter (D1)	1 mm	Collar diameter (D2)	2.1 mm

**Classifications**

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01		

**Approvals**

Approvals



ROHS Conform