

Bluetooth® Speaker | 45 W | Waterproof | Carrying Handle | Black / Black

General information

This Wireless Bluetooth® Speaker is made for outdoor listening – so get out there and party!

Portable

Incredibly lightweight and portable this speaker nevertheless deliver a heavyweight, deep and rich sound, with a maximum peak power output of 45 W.

Waterproof

And rain needn't stop play. The IPX5-rated waterproofing means all you need is an umbrella to dance and sing in the rain.

Long lasting

The integrated 4400 mAh battery gives you up to five hours of playback on a single charge – and you can carry on listening to your music as you recharge the speakers ready for the next outdoor party.

Features

- A lightweight speaker – offering 45 W peak power output – to deliver a heavyweight sound
- IPX5 waterproof rating – makes these ideal for use outdoors
- In-built 2x 2200 mAh battery – lets the music play for up to five hours at a time

Specifications

RMS:	15 W
Power rating:	5 V 1 A
Capacity:	4400 mAh
Frequency response:	20 Hz...20 kHz (±3 dB)
Sensitivity:	80 dB
Transmission power:	4 dB/m
True Wireless Stereo (TWS):	No
Peak output power:	45 W
Operating Distance:	10 m



Sales information

Order code:	SPBT35100BK
Product description:	Bluetooth® Speaker 45 W Waterproof Carrying Handle Black / Black
Packaging:	Giftbox
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	235x230x105	1140 gr.
5	260x260x535	6220 gr.



Bluetooth® Speaker | 45 W | Waterproof | Carrying Handle | Black / Black

Charging time:	3 h
Maximum Play Time:	5 hrs
Frequency min.:	2.402 GHz
Frequency range:	2.402...2.480 GHz
Impedance:	4 Ohm
Frequency max.:	2.480 GHz
Batteries included:	Built-In Lithium-Ion
Battery type:	Built-In Lithium-Ion
Colour:	Black/Black
Bluetooth version:	v4.1
Material:	ABS / Leather
Quantity:	1
Microphone:	Built-In Microphone
IP rating:	IPX5
Speaker channels:	Stereo
Power plug:	USB
Connection:	Bluetooth
Connection input:	1x Micro USB
Connection input:	1x 3.5 mm

Package contents

Bluetooth speaker
Quick installation guide