

## CUBE 20S DIGITAL OUTPUT MODULE DO2


2x230AC 3,0A Relais

Expansion module

DO2 - (E) 230 V AC Relais

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



### Internal communication

Module Supply	via system connection
Current consumption	max. 130 mA

### General data

Protection	IP20
Connection	Spring clamp plug-in terminals: max. 1.5 mm <sup>2</sup> (AWG 16)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

### Output

Actuator supply UA	max. 30 V DC/230 V AC
Switching current per output	max. 3 A (short-circuit and overload protected)
Galvanic isolation	500 V DC between outputs and internal communication

### Diagnostic

Communication status	via LED
Diagnostic via LED	per module and channel
Diagnostic via BUS	per module
Monitoring - under voltage	yes
Monitoring - no voltage	no
Short circuit and overload	yes

### Commercial data

country of origin	TH
customs tariff number	85364900
minimum order quantity	1