



SIMATIC ET 200SP, BASEUNIT BU20-P6+A2+4D BU-TYPE C0, PUSH-IN KLEMMEN, WITH 2 AUX-TERMINALS, NEW LOADGROUP, WXH: 20MMX117MM

Product type designation	
Supply voltage	
Rated value (DC)	24 V; 30 V
Rated value (AC)	230 V; 110 V
External protection of power supply lines	Yes; 10 A miniature circuit breaker with type B or C tripping characteristic for the respective rated supply voltage
Current carrying capacity	
up to 60 °C, max.	10 A
Galvanic isolation	
between backplane bus and supply voltage	Yes
Between process terminals and supply voltage	Yes
Isolation	
Isolation checked with	3250 V DC
Dimensions	
Width	20 mm
Height	117 mm
Weights	
Weight, approx.	47 g
last modified:	12.03.2015