



Datenblatt - Fiche technique - Data sheet


11.04.5518




ROLINE GOLD Monitorkabel DVI, ST-ST, (24+1) dual link, 10,0m

ROLINE GOLD Câble pour écran DVI, M-M, (24+1) dual link, 10,0m

ROLINE GOLD Monitor Cable, DVI (24+1), Dual Link, M/M, 10 m



PIN Assignment



ELECTRICAL TEST:

1. 100% OPEN SHORT & MIS WIRE TEST
2. CONTACT RESISTANCE: 5 OHM (MAX)
3. INSULATION RESISTANCE: 10M OHM (MIN)
4. HI-POT TEST: DC 300V/10ms

NO	DESCRIPTION	QTY	UNIT
13	Wire Clip OD:8.5mm	2	pcs
12	Ferrite core 28.5*17.5*11.5MM	2	pcs
11	DVI M TRANSPARENT DUST COVER	2	pcs
10	DVI 24# Yellow down Shell aluminium alloy laser etching DVI LOGO	2	pcs
9	DVI 24# Yellow up Shell aluminium alloy laser etching DVI LOGO	2	pcs
8	#4-40UNC 4*38.5 Gold-plated screws	4	pcs
7	TUBE BLACK : φ 1.5*22mm THICK	0.044	m
6	TUBE BLACK : φ 1.0*12mm THIN	0.188	m
5	BLACK Ø2.0*10mm THIN	0.14	m
4	45P BLACK PVC	40	g
3	TRANSPARENT PE	8	g
2	DVI(24+1) M SOLDER TYPE, GOLD PLATED SHELL , BLACK INSULATION	2	pcs
1	UL20276 (28AWG*1P+D+AL+MY)*7C+28AWG*1P+28AWG*3C+ADB(50%AL) OD:8.5mm WITH BLACK/YELLOW NET	10	M

TOLERANCE	INCHES/M/M	
	INCHES	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

rotronic

11.04.5518

ROLINE GOLD DVI Cable, Dual Link, M / M
10m, black w/yellow & black nylon net

DRAWN BY		SCALE	NONE	DRAWING NO:	REV A
CHECK BY		UNIT	MM		
APPD BY		DATE	2013.07.26		1/1