

**Tasten, Stößel 5.46 001.xxx  
aus Kunststoff für MICON**

**Farbe /0200 opak Standard**

**Farbe /1000 farblos (kundenspezifisch)**

Artikel-EndNr.	Benennung	Länge L	Ges. Bauhöhe GH	1.Verwendung
103	D6,0	3,0	5,55	MICON
104	D6,0	3,45	6,0	MICON
105	D6,0	3,95	6,5	MICON
106	D6,0	4,45	7,0	MICON
107	D6,0	7,15	9,7	MICON
108	D6,0	9,95	12,5	MICON
123	D8,0	3,0	5,55	MICON
124	D8,0	3,45	6,0	MICON
125	D8,0	3,95	6,5	MICON
126	D8,0	4,45	7,0	MICON
127	D8,0	7,15	9,7	MICON
128	D8,0	9,95	12,5	MICON
143	D11,5	3,0	5,55	MICON
144	D11,5	3,45	6,0	MICON
145	D11,5	3,95	6,5	MICON
146	D11,5	4,45	7,0	MICON
147	D11,5	7,15	9,7	MICON
148	D11,5	9,95	12,5	MICON
163	D14,5	3,0	5,55	MICON
164	D14,5	3,45	6,0	MICON
165	D14,5	3,95	6,5	MICON
166	D14,5	4,45	7,0	MICON
167	D14,5	7,15	9,7	MICON
168	D14,5	9,95	12,5	MICON
183	D19,0	3,0	5,55	MICON
184	D19,0	3,45	6,0	MICON
185	D19,0	3,95	6,5	MICON
186	D19,0	4,45	7,0	MICON
187	D19,0	7,15	9,7	MICON
188	D19,0	9,95	12,5	MICON