

## Husky<sub>RB4XMV/5</sub>



CE – certified to EMC directive 89/336/EEC.  
 Complies with low voltage directive 73/23/EEC.  
 High voltage transient and polarity reversal protected.  
 Operating temperature: -20°C to + 55°C.  
 Beacon should be operated in a vertical position with lens uppermost.



4lcd (amber)	75 flashes/min	10-100Vdc 30-60Vac	360mA	60mA	IP65	0.4kg

### Features:

A bright, multivoltage 5W Xenon beacon.

- Multivoltage 10 – 100 Vdc, 30 – 60 Vac
- Bright, intense Xenon flash
- Low power consumption
- 3,000+ hours tube life, 12 months' guarantee
- Replaceable Xenon tube
- Weatherproof to IP65

### Product options:

- Sounder plinth, fixes to base of beacon



FX29 Sounder Plinth  
Part No. 521047

### Applications:

Suitable for fork lift trucks and battery powered vehicles.

### Materials:

Polycarbonate lens, ABS base.

Amber	469012
Red	469013
Blue	469004
Clear	469011
Green	469005
	<p><b>Drilling for Panel Mounting (ISO 4148)</b></p>