

CONSTANT VOLTAGE LED DRIVER

24VDC 200WATT

POWERPAX: LED-DR-24V-200W

Features:

- Input Voltage 200-277vac
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 1 Year Warranty



Description:

The Range of 200 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-24V-200W
Output Voltage Rating	24vdc
Output Current Range	8.33A
Rated Power	200 Watt
Dimensions	220.8 x 61.5 x 36.5 mm
Input Voltage Range	200-277VAC
Input Voltage Frequency	50Hz/60Hz
Inrush Current	<75A
Input power	>230W
Efficiency	≥ 90 %
Power Consumption Without Load	<0.5W
Overload Protection	Ta, 0.94-1.06 times of input voltage, 1.7 times of rated power
Short Circuit Protection	Ta, 0.94-1.06 times of input voltage
Automatically Restart	Over load, short circuit revocation
Working Temperature	-40°C ~ +60°C
Relative Humidity	45% ~ 95%
MTBF	30000hr
EMC emission	EN55015
EMC Immunity	EN61000-4-2,3,4,5,6 EN61547
Safety Standards	EN61347-1, EN61347-2-13

POWERPAX

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

CONSTANT VOLTAGE LED DRIVER 24VDC 200WATT

POWERPAX: LED-DR-24V-200W

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

POWERPAX