

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2196802122](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead SL Female-to-SL Female, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Red

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                        |                                                 |
|------------------------|-------------------------------------------------|
| Product Family         | Cable Assemblies                                |
| Series                 | <a href="#">219680</a>                          |
| Application            | Signal, Wire-to-Board, Wire-to-Wire             |
| Assembly Configuration | Pre-crimped Lead Only                           |
| Connector to Connector | SL Crimp Terminals                              |
| Overview               | <a href="#">Off-the-Shelf Pre-Crimped Leads</a> |
| Product Name           | SL                                              |
| Taxonomy               | Power and Signal Cable Assembl                  |
| UPC                    | 195842871779                                    |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 150.00mm             |
| Circuits (Loaded)              | 1                    |
| Color - Resin                  | Red                  |
| Gender                         | Female-Female        |
| Lock to Mating Part            | Yes                  |
| Material - Metal               | Phosphor Bronze      |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 0.579/g              |
| Number of Rows                 | 1                    |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 3.750µm              |
| Plating min - Termination      | 3.750µm              |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 1.52mm max.          |
| Wire Size AWG                  | 24                   |
| Wire/Cable Type                | UL 11028             |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2196802121-000 |
|---------------|----------------|



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[219680 Series](#)

**Use With**

SL Crimp Housing [70066](#) , [70450](#)