

SPALT-BLECHLOCHER TRICUT®

Ø in mm	Max. Material- stärke in mm (S235)	Größe Metrisch	Größe PG	Größe Inch		Größe Conduit & Pipe Size				
				Art.-Nr.						
12,5	1,5	M 12	7	1/2"	0.500	-	01674	01770	02022	01334
15,2	2,0	-	9	-	0.598	-	01680	01771	02003	01339
16,2	2,0	M 16	-	-	0.638	-	01683	01772		
18,6	2,0	-	11	-	0.732	-	01686	01773		
20,4	2,0	M 20	13	-	0.803	-	01689	01774		
22,5	2,0	-	16	7/8"	0.886	1/2"	01692	01775		
25,4	2,0	M 25	-	1"	1.000	-	01695	01776		
28,3	2,0	-	21	-	1.114	3/4"	01698	01777		
28,3	3,0	-	21	-	1.114	3/4"	01701	01778	02002	01340
30,5	2,0	-	-	1-7/32"	1.201	-	01703	01779	02003	01339
32,5	3,0	M 32	-	-	1.280	-	01708	01780	02002	01340
34,6	3,0	-	-	1-11/32"	1.362	1"	01711	01788		
37,0	3,0	-	29	-	1.457	-	01713	01781		
40,5	3,0	M 40	-	-	1.594	-	01715	01782		
43,2	3,0	-	-	1-11/16"	1.701	1 1/4"	01718	01789		
47,0	3,0	-	36	-	1.850	-	01720	01783		
49,6	3,0	-	-	1-15/16"	1.953	1 1/2"	01723	01790		
50,5	3,0	M 50	-	-	1.988	-	01736	01784		
54,0	3,0	-	42	2-1/8"	2.126	-	01727	01785		
60,0	3,0	-	48	-	2.362	-	01729	01786		
61,5	3,0	-	-	2-3/8"	2.421	2"	01732	01791	01341	
63,5	3,0	M 63	-	2-1/2"	2.500	-	01739	01787		