



Quality Products. Service Excellence.

## Watertight Diecast Aluminum Enclosures 1550Z Series

cUL & UL Listed, Thick Wall

### Key Features:



- Thick-wall diecast aluminum watertight electronic instrument enclosure.
- Rugged, diecast aluminum alloy is tough yet easy to machine.
- Two piece tongue and groove construction for protection against access of dust and water.
- Easy to wallmount using blind thru-box holes (on all sizes except **1550Z102**, **1550Z115**, and **1550Z120**). Access to blind holes is outside of gasket ring to uphold ingress protection.
- Unpainted version is vibra finished for a smooth surface with no sharp edges.
- Textured black version is coated with tough polyester powder for a lasting finish, even after machining. Finish is applied outside and inside the enclosure.
- Lid is secured with either two, four, or six stainless steel Philips head machine screws, depending on enclosure size.
- Lid screws are outside the gasket protection area to eliminate the need for o-rings.
- Lid screws are self-captivating on six sizes: **1550Z107**, **1550Z108**, **1550Z116**, **1550Z117**, **1550Z137**, and **1550Z139**. Lid holes are slightly undersized and threaded with the first installation.
- Designed to meet IP66 (NEMA 1, 4, 4X, 12, and 13 ratings). Gasket is pre-formed, one-piece silicone rubber and installs easily into lid groove.
- Gasket has a temperature rating of -40°C to +150°C (-40°F to 302°F).
- North American Mark of Safety - cUL and UL listed. Certified to NEMA 4X standards (File #E71073).
- All sizes except 1550Z101 carry an impact rating of IK08 per IEC62262.
- No internal ribs for easy installation of connectors without interference or additional milling.

No internal ribs on the walls make connector installation easy.

Lid screws become captive once installed in lid.

Wallmounting holes are located outside the gasket perimeter.



### Accessories

- Breather Kit
- Small Rainproof Ventilator
- Pressure Compensation Plug
- Liquid-Tight, Strain Relief Cordgrips

## Enclosures

Part Number	Color	Length (mm)	Width (mm)	Total Depth (mm)	Lid Height (mm)	Replacement Lid	Replacement Ground	Replacement Gaskets
						Screw Pack	Screw Pack	(Pair)
1550Z101	Unpainted	50.00	45.00	30.00	6.00	SC1550Z103-50	SCG060-50	1550Z101GASKET
1550Z101BK	Black	50.00	45.00	30.00	6.00	SC1550Z103-50	SCG060-50	1550Z101GASKET
1550Z104	Unpainted	64.00	58.00	35.00	5.00	SC1550Z103-50	SCG060-50	1550Z104GASKET
1550Z104BK	Black	64.00	58.00	35.00	5.00	SC1550Z103-50	SCG060-50	1550Z104GASKET
1550Z102	Unpainted	90.00	36.00	30.00	5.00	SC1550Z102-50	SCG060-50	1550Z102GASKET
1550Z102BK	Black	90.00	36.00	30.00	5.00	SC1550Z102-50	SCG060-50	1550Z102GASKET
1550Z103	Unpainted	98.00	64.00	34.00	9.00	SC1550Z103-50	SCG060-50	1550Z103GASKET
1550Z103BK	Black	98.00	64.00	34.00	9.00	SC1550Z103-50	SCG060-50	1550Z103GASKET
1550Z106	Unpainted	115.00	65.00	30.00	5.00	SC1550Z103-50	SCG060-50	1550Z106GASKET
1550Z106BK	Black	115.00	65.00	30.00	5.00	SC1550Z103-50	SCG060-50	1550Z106GASKET
1550Z111	Unpainted	115.00	65.00	55.00	5.00	SC1550Z103-50	SCG060-50	1550Z106GASKET
1550Z111BK	Black	115.00	65.00	55.00	5.00	SC1550Z103-50	SCG060-50	1550Z106GASKET
1550Z113	Unpainted	115.00	90.00	55.00	5.00	SC1550Z103-50	SCG060-50	1550Z113GASKET
1550Z113BK	Black	115.00	90.00	55.00	5.00	SC1550Z103-50	SCG060-50	1550Z113GASKET
1550Z137	Unpainted	121.00	121.00	102.00	20.50	SC1550Z116-30	SCG060-50	1550Z137GASKET
1550Z137BK	Black	121.00	121.00	102.00	20.50	SC1550Z116-30	SCG060-50	1550Z137GASKET
1550Z107	Unpainted	125.00	80.00	41.00	16.00	SC1550Z107-50	SCGM4-50	1550Z107GASKET
1550Z107BK	Black	125.00	80.00	41.00	16.00	SC1550Z107-50	SCGM4-50	1550Z107GASKET
1550Z108	Unpainted	125.00	80.00	59.00	16.00	SC1550Z107-50	SCGM4-50	1550Z107GASKET
1550Z108BK	Black	125.00	80.00	59.00	16.00	SC1550Z107-50	SCGM4-50	1550Z107GASKET
1550Z115	Unpainted	148.00	108.00	75.00	10.00	SC1550Z103-50	SCG060-50	1550Z115GASKET
1550Z115BK	Black	148.00	108.00	75.00	10.00	SC1550Z103-50	SCG060-50	1550Z115GASKET
1550Z109	Unpainted	150.00	64.00	36.00	10.00	SC1550Z103-50	SCG060-50	1550Z109GASKET
1550Z109BK	Black	150.00	64.00	36.00	10.00	SC1550Z103-50	SCG060-50	1550Z109GASKET
1550Z139	Unpainted	159.00	159.00	102.00	20.50	SC1550Z116-30	SCG060-50	1550Z139GASKET
1550Z139BK	Black	159.00	159.00	102.00	20.50	SC1550Z116-30	SCG060-50	1550Z139GASKET
1550Z116	Unpainted	160.00	100.00	60.00	20.00	SC1550Z116-30	SCGM4-50	1550Z116GASKET
1550Z116BK	Black	160.00	100.00	60.00	20.00	SC1550Z116-30	SCGM4-50	1550Z116GASKET
1550Z117	Unpainted	160.00	100.00	81.00	20.00	SC1550Z116-30	SCGM4-50	1550Z116GASKET
1550Z117BK	Black	160.00	100.00	81.00	20.00	SC1550Z116-30	SCGM4-50	1550Z116GASKET
1550Z120	Unpainted	171.00	121.00	55.00	10.00	SC1550Z103-50	SCG060-50	1550Z120GASKET
1550Z120BK	Black	171.00	121.00	55.00	10.00	SC1550Z103-50	SCG060-50	1550Z120GASKET
1550Z124	Unpainted	222.50	146.50	55.00	5.00	SC1550Z103-50	SCG060-50	1550Z124GASKET
1550Z124BK	Black	222.50	146.50	55.00	5.00	SC1550Z103-50	SCG060-50	1550Z124GASKET
1550Z220	Unpainted	222.50	146.50	82.50	32.50	SC1550Z220-30	SCG060-50	1550Z124GASKET
1550Z220BK	Black	222.50	146.50	82.50	32.50	SC1550Z220-30	SCG060-50	1550Z124GASKET

Tags: thick wall, diecast, outdoor, nema

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.