

SMC-37

(2 Flaps FL16/10) 32 Werte / 4.800Stück

Chip-Kerko

Type/Fab: C0402 / Phycomp, Kemet oder Alternative

Baugröße/Volt : 0402 / 50V

Menge: je 150 Stück / Wert

Werte – Mengenverteilung:

0,47 (0,5) pF COG $\pm 0,25$ pF	1,0pF COG $\pm 0,25$ pF	1,5pF COG $\pm 0,25$ pF	2,2pF COG $\pm 0,25$ pF
3,3pF COG $\pm 0,25$ pF	4,7pF COG $\pm 0,25$ pF	6,8pF COG $\pm 0,5$ pF	10pF COG $\pm 5\%$
15pF COG $\pm 5\%$	22pF COG $\pm 5\%$	33pF COG $\pm 5\%$	47pF COG $\pm 5\%$
68pF COG $\pm 5\%$	100pF COG $\pm 5\%$	120 pF COG $\pm 5\%$	150pF COG $\pm 5\%$
220pF COG $\pm 5\%$	330pF COG $\pm 5\%$	470pF X7R $\pm 5\%$	680pF X7R $\pm 5\%$
150pF X7R $\pm 10\%$	220pF X7R $\pm 10\%$	330pF X7R $\pm 10\%$	470pF X7R $\pm 10\%$
680pF X7R $\pm 10\%$	1000pF X7R $\pm 10\%$	1500pF X7R $\pm 10\%$	2200pF X7R $\pm 10\%$
3300pF X7R $\pm 10\%$	4700pF X7R $\pm 10\%$	6800pF X7R $\pm 10\%$	10.000pF X7R $\pm 10\%$