

## Features

- Rugged Flexible whip antenna
- MR – Right-angled SMA antenna
- MS – Straight SMA antenna



## Electrical Specification

|                   |                                    |
|-------------------|------------------------------------|
| Radiating Element | ¼ Wave whip - requires groundplane |
| Frequency Range   | 410–433 (MHz)                      |
| Impedance         | 50Ω                                |
| VSWR              | 2.33 dBi                           |
| Gain              | 7.9 dBi                            |
| Maximum Power     | 50(w)                              |
| Connector Type    | SMA-Right angle/Straight           |

## Mechanical Specification

|        | Right Angled (MR) | Straight (MS) |
|--------|-------------------|---------------|
| Length | 130mm             | 130mm         |
| Weight | 8.5g              | 6.1g          |

## Order codes

|           |                               |
|-----------|-------------------------------|
| ANT-433MR | Right angled SMA whip antenna |
| ANT-433MS | Straight SMA whip antenna     |