



Datenblatt - Fiche technique - Data sheet

11.04.5612




ROLINE DisplayPort Kabel DP ST - DVI ST, 5,0m

ROLINE Câble DisplayPort DP M - DVI M, 5,0m


ROLINE DisplayPort Cable, DP-DVI (24+1), M/M, 5 m

5000±50MM




ELECTRICAL TEST:

1. 100% OPEN SHORT SHORT & MIS WIRE TEST
2. CONTACT RESISTANCE: 1 OHM(MAX)
3. INSULATION RESISTANCE: 10M OHM(MIN)
4. HI-POT TEST: DC 300V/10ms



PIN ASSIGNMENT



NO	CELINK P/N	DESCRIPTION	Q'TY	UNIT
13	A6-0000099	DisplayPort TRANSPARENT DUST COVER	1	pcs
12	A6-0000025	DVI M TRANSPARENT DUST COVER	1	pcs
11	A6-R071085	DISPLAY PORT M ABS BOTTOM SHELL	1	pcs
10	A6-R071084	DISPLAY PORT M ABS TOP SHELL	1	pcs
9	A10-R043162	H.S.T:Ø1.5*42mm.	1	pcs
8	A10-R075147	H.S.T:Ø1.0*10mm.	8	pcs
7	A10-R075130	H.S.T:Ø2.5*10mm.	8	pcs
6	A7-R040001	SCREW:#4-40UNC(2.8*45MM) NICKEL	2	pcs
5	A5-R047001	PVC 45P COLOR:BLACK	38	g
4	A5-R047011	TRANSPARENT PE	5	g
3	A2-R020051	DVI(24+1) M SOLDER TYPE,NICKEL PLATED,BLACK INSULATION	1	pcs
2	A78-0000080	DISPLAY PORT M+PCB+SMT	1	set
1	A4-R001376	UL20276(30AWG*1PR+EAM)*4C+30AWG*1PR+30AWG*3C+AEB(AL) OD:5.5MM BLACK JACKET	5	M
NO	CELINK P/N	DESCRIPTION	Q'TY	UNIT

REV.	DESCRIPTION	DATE
.X	TOLERANCE INCHES .015	
.XX	M/M .30	
.XXX	.010	
	.005	
	.05	
	DRAWN BY	
	CHECK BY	
	APPD BY	
	CUSTOMER P/N :	11.04.5612
	SCALE	NONE
	UNIT	MM
	DATE	07.04/09
	DRAWING NO.:	CA1790009
	REV.	A
		1/6

Rotronic Co., Ltd.

ROLINE Display to DVI Cable, DP M - DVI 5M, black